M2 Series Application Guide - Speed & Feed (inch)

ISO Code	Work Material	Type of Cut	Axial DOC	Radial DOC	Number of Flutes	Speed	Feed (Inch per Tooth)									
						(SFM)	1/8	3/16	1/4	5/16	3/8	1/2	5/8	3/4	1	
N	Aluminum Alloys 2024, 6061, 7075	Slotting	1 x D	1 x D	2	800	.0015	.0023	.0030	.0038	.0045	.0060	.0075	.0090	.0120	
		Peripheral - Rough	1 x D	.75 x D	2	1000	.0019	.0028	.0038	.0047	.0056	.0075	.0094	.0113	.0150	
		Peripheral - Finish	1.5 x D	.01 x D	2	1200	.0024	.0035	.0047	.0059	.0071	.0094	.0118	.0141	.0188	
	High Silicon Aluminum A380, A390	Slotting	.75 x D	1 x D	2	500	.0013	.0020	.0026	.0033	.0039	.0052	.0065	.0078	.0104	
		Peripheral - Rough	1 x D	.5 x D	2	700	.0016	.0024	.0033	.0041	.0049	.0065	.0081	.0098	.0130	
		Peripheral - Finish	1.5 x D	.01 x D	2	900	.0020	.0031	.0041	.0051	.0061	.0082	.0102	.0122	.0163	
	Magnesium Alloys	Slotting	1 x D	1 x D	2	800	.0015	.0023	.0030	.0038	.0045	.0060	.0075	.0090	.0120	
		Peripheral - Rough	1 x D	.75 x D	2	1000	.0019	.0028	.0038	.0047	.0056	.0075	.0094	.0113	.0150	
		Peripheral - Finish	1.5 x D	.01 x D	2	1200	.0024	.0035	.0047	.0059	.0071	.0094	.0118	.0141	.0188	
	Copper Alloys Brass, Bronze	Slotting	.75 x D	1 x D	2	500	.0013	.0020	.0026	.0033	.0039	.0052	.0065	.0078	.0104	
		Peripheral - Rough	1 x D	.75 x D	2	575	.0016	.0024	.0033	.0041	.0049	.0065	.0081	.0098	.0130	
		Peripheral - Finish	1.5 x D	.01 x D	2	650	.0020	.0031	.0041	.0051	.0061	.0082	.0102	.0122	.0163	
	Composites Plastics, Fiberglass	Slotting	1 x D	1 x D	2	500	.0013	.0020	.0026	.0033	.0039	.0052	.0065	.0078	.0104	
		Peripheral - Rough	1 x D	.75 x D	2	700	.0016	.0024	.0033	.0041	.0049	.0065	.0081	.0098	.0130	
		Peripheral - Finish	1.5 x D	.01 x D	2	900	.0020	.0031	.0041	.0051	.0061	.0082	.0102	.0122	.0163	
	Aluminum Alloys 2024, 6061, 7075	Slotting	.75 x D	1 x D	3	800	.0013	.0020	.0026	.0033	.0039	.0052	.0065	.0078	.0104	
		Peripheral - Rough	1 x D	.75 x D	3	1000	.0016	.0024	.0033	.0041	.0049	.0065	.0081	.0098	.0130	
		Peripheral - Finish	1.5 x D	.01 x D	3	1200	.0020	.0031	.0041	.0051	.0061	.0082	.0102	.0122	.0163	
	High Silicon Aluminum A380, A390	Slotting	.5 x D	1 x D	3	500	.0011	.0017	.0022	.0028	.0033	.0044	.0055	.0066	.0088	
		Peripheral - Rough	1 x D	.5 x D	3	700	.0014	.0021	.0028	.0034	.0041	.0055	.0069	.0083	.0110	
		Peripheral - Finish	1.5 x D	.01 x D	3	900	.0017	.0026	.0035	.0043	.0052	.0069	.0086	.0104	.0138	
	Magnesium Alloys	Slotting	.75 x D	1 x D	3	800	.0013	.0020	.0026	.0033	.0039	.0052	.0065	.0078	.0104	
		Peripheral - Rough	1 x D	.75 x D	3	1000	.0016	.0024	.0033	.0041	.0049	.0065	.0081	.0098	.0130	
		Peripheral - Finish	1.5 x D	.01 x D	3	1200	.0020	.0031	.0041	.0051	.0061	.0082	.0102	.0122	.0163	
	Copper Alloys Brass, Bronze	Slotting	.75 x D	1 x D	3	500	.0011	.0017	.0022	.0028	.0033	.0044	.0055	.0066	.0088	
		Peripheral - Rough	1 x D	.75 x D	3	575	.0014	.0021	.0028	.0034	.0041	.0055	.0069	.0083	.0110	
		Peripheral - Finish	1.5 x D	.01 x D	3	650	.0017	.0026	.0035	.0043	.0052	.0069	.0086	.0104	.0138	
	Composites Plastics, Fiberglass	Slotting	1 x D	1 x D	3	500	.0011	.0017	.0022	.0028	.0033	.0044	.0055	.0066	.0088	
		Peripheral - Rough	1 x D	.75 x D	3	700	.0014	.0021	.0028	.0034	.0041	.0055	.0069	.0083	.0110	
	i iastics, i ibergiass	Peripheral - Finish	1.5 x D	.01 x D	3	900	.0017	.0026	.0035	.0043	.0052	.0069	.0086	.0104	.0138	

D = Tool Diameter

- ≈ Approximately Equals≤ Less Than≤ Less Than or Equal To> Greater Than
- ≤ Less Than or Equal To > Greater ≥ Greater Than or Equal To = Equals
- × Multiply

Common Machining Formulas

 $RPM = \frac{SFM \times 3.82}{}$

 $SFM = RPM \times D \times .262$

 $IPM = RPM \times IPT \times Z$

 $MRR = RDOC \times ADOC \times IPM$

M/min x 318.3 $M/min = RPM \times D \times .00314$

 $MMPM = RPM \times MMPT \times Z$ $MRR = RDOC \times ADOC \times MMPM$

