M904 Application Guide - Speed & Feed (inch)

ISO Code	Work Material	Type of Cut	Axial DOC	Radial DOC	Number of Flutes	Speed	Feed (Inches per Tooth)											
						(SFM)	1/8	5/32	3/16	7/32	1/4	5/16	3/8	7/16	1/2	5/8	3/4	1
K	Cast Iron Gray	Slotting	1 x D	1 x D	4	325	.0006	.0008	.0009	.0011	.0012	.0015	.0018	.0021	.0024	.0030	.0036	.0048
		Peripheral - Rough	1.25 x D	.5 x D	4	400	.0008	.0009	.0011	.0013	.0015	.0019	.0023	.0026	.0030	.0038	.0045	.0060
		Finish	1.5 x D	.015 x D	4	475	.0008	.0010	.0012	.0014	.0017	.0021	.0025	.0029	.0033	.0041	.0050	.0066
	Cast Iron Ductile	Slotting	1 x D	1 x D	4	300	.0006	.0007	.0008	.0010	.0011	.0014	.0017	.0019	.0022	.0028	.0033	.0044
		Peripheral - Rough	1.25 x D	.5 x D	4	375	.0007	.0008	.0010	.0012	.0014	.0017	.0020	.0024	.0027	.0034	.0041	.0054
		Finish	1.5 x D	.015 x D	4	450	.0008	.0009	.0011	.0013	.0015	.0019	.0023	.0026	.0030	.0038	.0045	.0060
	Cast Iron Malleable	Slotting	.75 x D	1 x D	4	250	.0006	.0007	.0008	.0010	.0011	.0014	.0017	.0019	.0022	.0028	.0033	.0044
		Peripheral - Rough	1.25 x D	.5 x D	4	325	.0007	.0008	.0010	.0012	.0014	.0017	.0020	.0024	.0027	.0034	.0041	.0054
		Finish	1.5 x D	.015 x D	4	400	.0008	.0009	.0011	.0013	.0015	.0019	.0023	.0026	.0030	.0038	.0045	.0060
P	Low Carbon Steels 1018, 12L14, 8620	Slotting	1 x D	1 x D	4	350	.0007	.0008	.0010	.0011	.0013	.0016	.0020	.0023	.0026	.0033	.0039	.0052
		Peripheral - Rough	1.25 x D	.5 x D	4	425	.0008	.0010	.0012	.0014	.0016	.0020	.0024	.0028	.0032	.0040	.0048	.0064
		Finish	1.5 x D	.015 x D	4	500	.0009	.0011	.0014	.0016	.0018	.0023	.0027	.0032	.0036	.0045	.0054	.0072
	Medium Carbon Steels 4140, 4340	Slotting	1 x D	1 x D	4	300	.0006	.0008	.0009	.0011	.0012	.0015	.0018	.0021	.0024	.0030	.0036	.0048
		Peripheral - Rough	1.25 x D	.5 x D	4	375	.0008	.0009	.0011	.0013	.0015	.0019	.0023	.0026	.0030	.0038	.0045	.0060
		Finish	1.5 x D	.015 x D	4	450	.0008	.0010	.0012	.0014	.0017	.0021	.0025	.0029	.0033	.0041	.0050	.0066
	Tool & Die Steels <48 Rc A2, D2, H13, P20	Slotting	.75 x D	1 x D	4	300	.0006	.0008	.0009	.0011	.0012	.0015	.0018	.0021	.0024	.0030	.0036	.0048
		Peripheral -Rough	1.25 x D	.3 x D	4	375	.0007	.0009	.0011	.0013	.0015	.0018	.0022	.0025	.0029	.0036	.0044	.0058
		Finish	1.5 x D	.015 x D	4	450	.0008	.0009	.0011	.0013	.0015	.0019	.0023	.0026	.0030	.0038	.0045	.0060
M	Martensitic Stainless Steels 416, 410, 440C	Slotting	.75 x D	1 x D	4	300	.0006	.0008	.0009	.0011	.0012	.0015	.0018	.0021	.0024	.0030	.0036	.0048
		Peripheral - Rough	1.25 x D	.3 x D	4	375	.0007	.0009	.0011	.0013	.0015	.0018	.0022	.0025	.0029	.0036	.0044	.0058
		Finish	1.5 x D	.015 x D	4	450	.0008	.0009	.0011	.0013	.0015	.0019	.0023	.0026	.0030	.0038	.0045	.0060
	Austenitic Stainless Steels 303, 304, 316	Slotting	.75 x D	1 x D	4	275	.0007	.0008	.0010	.0011	.0013	.0016	.0020	.0023	.0026	.0033	.0039	.0052
		Peripheral - Rough	1.25 x D	.3 x D	4	325	.0008	.0010	.0012	.0014	.0016	.0020	.0024	.0028	.0032	.0040	.0048	.0064
		Finish	1.5 x D	.015 x D	4	400	.0008	.0010	.0012	.0014	.0017	.0021	.0025	.0029	.0033	.0041	.0050	.0066
	Precipitation Hardening Stainless Steel	Slotting	.5 x D	1 x D	4	250	.0005	.0006	.0008	.0009	.0010	.0013	.0015	.0018	.0020	.0025	.0030	.0040
		Peripheral - Rough	1.25 x D	.3 x D	4	300	.0006	.0008	.0009	.0011	.0013	.0016	.0019	.0022	.0025	.0031	.0038	.0050
	17-4, 15-5	Finish	1.5 x D	.015 x D	4	375	.0007	.0008	.0010	.0011	.0013	.0016	.0020	.0023	.0026	.0033	.0039	.0052
S	Titanium Alloys 6AL - 4V	Slotting	.5 x D	1 x D	4	250	.0005	.0006	.0008	.0009	.0010	.0013	.0015	.0018	.0020	.0025	.0030	.0040
		Peripheral - Rough	1.25 x D	.3 x D	4	300	.0006	.0008	.0009	.0011	.0013	.0016	.0019	.0022	.0025	.0031	.0038	.0050
		Finish	1.5 x D	.015 x D	4	375	.0007	.0008	.0010	.0011	.0013	.0016	.0020	.0023	.0026	.0033	.0039	.0052
	High Temperature Alloys Inconel, Haynes, Stellite, Hastalloy	Slotting	.25 x D	1 x D	4	60	.0005	.0007	.0008	.0009	.0011	.0013	.0016	.0018	.0021	.0026	.0032	.0042
		Peripheral - Rough	1.25 x D	.25 x D	4	90	.0007	.0008	.0010	.0012	.0014	.0017	.0020	.0024	.0027	.0034	.0041	.0054
	inconei, riayries, stellite, riastalloy	Finish	1.5 x D	.01 x D	4	125	.0008	.0010	.0012	.0014	.0016	.0019	.0023	.0027	.0031	.0039	.0047	.0062

D = Tool Diameter

≈ Approximately Equals

< Less Than

≤ Less Than or Equal To > Greater Than

≥ Greater Than or Equal To = Equals

× Multiply

Common Machining Formulas

 $RPM = \frac{SFM \times 3.82}{D}$

 $SFM = RPM \times D \times .262$

 $IPM = RPM \times IPT \times Z$

 $MRR = RDOC \times ADOC \times IPM$

D Tool Diameter

Z Number of Flutes

RPM Revolutions per Minute

SFM Surface Feet per Minute


IPM Inches per Minute

IPT Inch per Tooth

MRR Metal Removal Rate

RDOC Radial Depth of Cut

ADOC Axial Depth of Cut



Tool Tech Support

Information on tips and adjustments for the following milling operations can be found in our Technical Resources section beginning on page 129.

- HEM slotting
- Face milling
- Helical entry ramping
- Straight line ramping
- Long tool projection adjustments
- Ball nose milling adjustments
- Other helpful tips and calculations